

New improved range of high performance SKF grease

For longer service life

High performance ULTRA PREMIUM lithium complex premium grease

VKG IP PLUS (80 000* kilometers)



Features:

- Lithium based multi purpose gel grease with longer life.
- Excellent water resistance properties and NLGI Grade 3.
- Outstanding shear and rolling stability in operating temperature upto 180 °C.
- Recommended for all type of automotive applications in heavy commercial vehicles, buses, tractors, earth moving or agricultural equipment and heavily loaded bearings under extreme pressure conditions.

Benefits:

- Better life (upto 80 000 kms*) and high performance.
- Longer service life and longer component life.
- Less vehicle downtime for maintenance and lubrication – More miles will bring more smiles.

High performance lithium complex PREMIUM grease

VKG IP (60 000* kilometers)



Features:

- Lithium based premium multi purpose grease with better life.
- Recommended for all type of automotive applications in commercial and passenger vehicles, tractors, cars, earth-moving or agricultural equipment and heavily loaded bearings under extreme pressure conditions.
- Outstanding shear and rolling stability in operating temperature up to 160 °C.
- Superior water resistance properties and NLGI Grade 3.

Benefits:

- Better life (upto 60 000 kms*) and high performance.
- Longer service life and longer component life.
- Less vehicle downtime for maintenance and lubrication.

High performance lithium complex PREMIUM grease

VKG IN (20 000* kilometers)



Features:

- Excellent rust and oxidation resistance with better water washout properties and NLGI Grade 3.
- Improved mechanical and thermal stability in operating temperature up to 120 °C.
- Meets IS 12203:2004 specification.
- More suitable for two-wheelers, three-wheelers, small cars, available in 100 g till 180 kg barrels.

Benefits:

- Improved SKF IN grease.
- 20 000 kms* lubrication life.

* Under standard operating and testing conditions.

Install confidence, install SKF!



SKF grease price list (Effective from 1st June, 2021)

Grease variant	Product designation	Box qty.	Grease wt.	MRP (In Rs.)	Mechanic Incentive points
Normal Grease	VKG 9/0.1 IN	60	100 G	75	-
Normal Grease	VKG 9/0.2 IN	60	200 G	140	-
Normal Grease	VKG 9/0.5 IN	24	500 G	336	5
Normal Grease	VKG 9/1 IN	12	1 Kg	660	10
Normal Grease	VKG 9/2 IN	6	2 Kg	1300	20
Normal Grease	VKG 9/3 IN	4	3 Kg	1929	30
Normal Grease	VKG 9/5 IN	2	5 Kg	3235	50
Normal Grease	VKG 9/20 IN	1	20 Kg	12800	120
Normal Grease	VKG 9/180 IN	1	180 Kg	113580	150
Premium Grease	VKG 9/0.5 IP	24	500 G	350	5
Premium Grease	VKG 9/1 IP	12	1 Kg	680	10
Premium Grease	VKG 9/3 IP	4	3 Kg	2010	30
Premium Grease	VKG 9/5 IP	2	5 Kg	3300	50
Premium Grease	VKG 9/20 IP	1	20 Kg	13000	120
Premium Grease	VKG 9/180 IP	1	180 Kg	115200	180
Premuum Plus Grease	VKG 9/0.5 IP PLUS	24	500 G	410	5
Premuum Plus Grease	VKG 9/1 IP PLUS	12	1 Kg	800	10
Premuum Plus Grease	VKG 9/3 IP PLUS	4	3 Kg	2370	30
Premuum Plus Grease	VKG 9/5 IP PLUS	2	5 Kg	3900	50
Premuum Plus Grease	VKG 9/7 IP PLUS	2	7 Kg	5425	70
Premuum Plus Grease	VKG 9/20 IP PLUS	1	20 Kg	15400	120
Premuum Plus Grease	VKG 9/180 IP PLUS	1	180 Kg	136800	150

Install confidence, install SKF!

skf.com

©SKF is a registered trademark of the SKF Group.

©SKF Group 2021

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB 80/D9 18600 EN · June 2021

Version 3

Scan QR code
for any support



<https://bit.ly/37VQY1b>