

SKF timing belts

With high tensile strength wire

Features




OE equivalent quality



High strength tensile cord



Resistance to heat and oil



High load-carrying capacity



Perfect fit for continuous running



Install confidence,
install SKF!

The timing belt is a critical component within your vehicle. Investing in a high-quality timing belt can reduce the total maintenance cost, maintain better fuel efficiency and provide hassle-free power transmission for years with minimum costs. At SKF, we provide a complete range of standard and high-performance timing belts that are designed for easy installation in your vehicle.

Sr. no.	Designation	Name of mfg.	Model	No. of teeth	Width (mm)	Type	Size for SKF	Case qty.	Coupon	MRP
1	VKMT 55211	Ashok Leyland	Dost	124	25.4	HSN	PRM 124-25.4 HSN	35	10	741
2	VKMT 55109	Daewoo	Matiz	107	25.4	CR	YU 107-25	60	15	632
3	VKMT 55212	Fiat/Tata	Linea/Punto-Petrol/Vista/Manza-Petrol	124	22	HSN	YS 124-22 HSN	35	5	721
4	VKMT 55217	Ford	Ford-Classic/Fiesta/Figo (DV 4-Diesel)	144	25	HSN	PR 144-25 HSN	35	20	1308
5	VKMT 55216	Ford	Ford-Classic New/Ecosport/Fiesta New (DV 5-Diesel)	141	25.4	HSN	PRM 141-25.4 HSN	35	20	1923
6	VKMT 55207	GM	Chevrolet-Spark/U-VA	109	25.4	HSN	YU 109-25.4 HSN	60	15	984
7	VKMT 55110	HM	Chevrolet-Spark/U-VA			CR	YU 109-25.4	60	10	596
8	VKMT 55206	Honda	City (1.3/1.5)/Civic (1.5)	103	24	HSN	PRM 103-24 HSN	35	10	671
9	VKMT 55106	Hyundai	Santro	101	20	CR	YU 101-20	60	20	530
10	VKMT 55209	Mahindra	Logan/Vibe/Verito (K9K-1.5 Diesel)/Stile (K9K-1.5 Diesel)	123	27	HSN	PRM 123-27 HSN	35	20	1495
11	VKMT 55115	Maruti	800/Omni/Gypsy (Old)	88	19	CR	ZA 88-19	60	10	257
12	VKMT 55107	Maruti	Alto/Wagon-R	106	25.4	CR	YU 106-25	60	20	545
13	VKMT 55117	Maruti	Eeco/Esteem/Gypsy/Versa/Zen-MPFI	97	25.4	CR	PRM 97-25.4	35	20	552
14	VKMT 55219	Maruti	Esteem/Zen-2 Valve	89	25.4	HSN	ZH 89-25 HSN	60	10	704
15	VKMT 55116	Maruti	Esteem/Zen-2 Valve			CR	ZH 89-25	60	20	550
16	VKMT 55214	Maruti	Ace/Magic/Estate/Indica/Indigo/Mobile/Sumo/Winger	136	25.4	HSN	ZH 136-25 HSN	35	10	867
17	VKMT 55113	Maruti	Ace/Magic/Estate/Indica/Indigo/Mobile/Sumo/Winger			CR	ZH 136-25	35	5	478
18	VKMT 55108	Tata	Ace-CNG and Indica/Indigo-Petrol	106	24	CR	ZH 106-24	60	20	578
19	VKMT 55210	Tata	Ace-Dicor/Mega	123	19	HSN	ZH 123-19 HSN	35	5	569
20	VKMT 55208	Tata	Nano	115	15	HSN	YU 115-15 HSN	60	15	564
21	VKMT 55218	Tata	Aria/Hexa/Safari/Storme/Winger/Xenon-2.2 L	153	25.4	HSN	ZH 153-25.4 HSN	35	20	1689
22	VKMT 55215	Tata	Super Ace/Venture	138	25.4	HSN	ZH 138-25.4 HSN	35	5	844
23	VKMT 55114	Tata	Super Ace/Venture			CR	ZH 138-25.4	35	5	504
24	VKMT 55220	Toyota	Hiace/Hilux/Innova/Land Cruiser (2.5/3.0)	97	25.4	HSN	ZH 97-25 HSN	60	20	937
25	VKMT 55213	Toyota	Hiace/Hilux/Land Crusier/Qualis (2.4)	129	31	HSN	ZH 129-31 HSN	35	10	1146
26	VKMT 55112	Toyota	Hiace/Hilux/Land Crusier/Qualis (2.4)			CR	ZH 129-31	35	10	757

For more details/information, write to: Marketing department, Vehicle Service Market,

SKF India Limited

Chinchwad, Pune- 411 033

Tel: +91-20-6611 2500, Fax: +91-20-6611 2440

Helpline: 1800 222 007 (Toll free from MTNL/BSNL landlines)

or +91-22-6633 7777 (Normal STD charges apply)

Website: www.skfindia.com

CIN: L29130MH1961PLC011980

© SKF and Lincoln are registered trademarks of the SKF Group.

© SKF Group 2020

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB 80/P5 19011 EN.IN • November 2020

Certain image(s) used under license from Shutterstock.com.