Valve stem seals

Fit and forget

Why choose SKF Valve stem seals?

Robust product design


Longer product life

Controlled lubrication

Low oil consumption

Preferred choice for major OEMs

Compatible with a wide range of OEMs and aftermarket oils



Also available for two-wheelers



Install confidence, install SKF!





Valve stem seals

Segment	VSM part no.	Vehicle manufacturer	Vehicle model	Application	Product dimensions
Commercial vehicle	VKS 7273	Volvo Eicher	E494 4V 4CYL 3.8L BS VI engine/E474 2V 4CYL (110-140 HP) 2.8L BS VI engine/E366 2V 3CYL 1.8L (80-100HP) BS VI engine	Valve stem seal	6x8.8x10
Commercial vehicle	VKS 7278	Ashok Leyland	Ashok Leyland Hino/H Series (1616, 1616 XL, 1616 XP, Ecomet 1212, Ecomet 1012, U1616T, 1616 XP, U2523T, U2518T, 2516 TIL, 3123 XL, 3118 XP, 3118 XL, 3116 XL, 3116) IL, 2516IL/1, 2518 XP, 2518 XL, 2516IL, 4923, U4923 TT, 4023 XP, U4023 TT, 3518, U3518 TT)	Valve stem seal	9x13x11.5
Commercial vehicle	VKS 7281	Ashok Leyland	Neptun VI engine	Valve stem seal	8x13.5x16x14.7
Commercial vehicle	VKS 6906	Tata Motors Ltd.	ACE HT, EX, CNG, Magic Super Ace Bus-9.6T LPO NAC 12V, 9.6T LPO AMT 24V, 9.6T LP G2 AC, Trucks-1014 BSIII, 814 24V EIII SA, 814 24V EIV	Valve stem seal	7x11x4.4x9.5
Commercial vehicle	VKS 6915	Tata Motors Ltd.	All LCV/MCV/HCV with Tata engines 497 (407, 709, 909, 1109, Ultra 612, 812, 912, 1012, 1112)/697 (SK 1613, LPT 1613, LP 1613)/4SP (Xenon Plickup, Xenon Dicore Pickup, Xenon Crew Cab, Xenon Yodha, 407, LP 410, SFC 410, Ultra Bus 105, 269)	Valve stem seal (Inlet)	9x12x15.4x10.5
Commercial vehicle	VKS 6917	Tata Motors Ltd.	All LCV/MCV/HCV with Tata engines 497 (407, 709, 909, 1109, Ultra 612, 812, 912, 1012, 1112)/697 (SK 1613, LPT 1613, LP 1613)/4SP (Xenon Pickup, Xenon Dicore Pickup, Xenon Crew Cab, Xenon Yodha, 407, LP 410, SFC 410, Ultra Bus 105, 269)/Kirloskar SL 90	Valve stem seal (Exhaust valve)	10x12.8x16.2x10
Commercial vehicle	VKS 6918	Tata Motors Ltd.	2.2 LT Super Ace Mint/Xenon HT	Valve stem seal	6x8.8x12.2x10
Commercial vehicle	VKS 6972	Ashok Leyland	Hippo, Beaver (AL 680 Engine)	Valve stem seal	11x14x18x14
Commercial vehicle	VKS 7266	Mahindra & Mahindra Ltd.	Truxo 25, 31, 37, Torro 25, Traco 35, 40	Valve stem seal	7 x11 x11.5
Tractor	VKS 7288	John Deere	3029 engine (3 cylinder engine) 5E/5D/5C	Valve stem seal	7.9x13x14.7
Tractor	VKS 6917	Mahindra & Mahindra Ltd./ Escorts Limited	FT 60, FT 65, FT 70, FT 80/Mahindra Swaraj engine	Valve stem seal (Exhaust valve)	10x12.8x16.2x10
Tractor	VKS 6956	TAFE/Sonalika	30 DI, 35 DI, Gajraj, 42 DI, 45 Dio, DI 750, Simpson engine	Valve stem seal	8x10.8x14.2x10
Tractor	VKS 6963	Escorts Limited	FT 35, FT 45, Josh, Powertrac 434, 439	Valve stem seal	8x12x15.4x9.5
Tractor	VKS 6969	Escorts Limited	FT 60, FT 65, FT 70, FT 80	Valve stem seal	9x11.8x15.2x10
Car	VKS 7273	Tata Motors	1.5 LT Crail diesel engine (Tiago/Tigor/Altroz/Nexon)	Valve stem seal	6x8.8x10
Car	VKS 7274	Maruti Suzuki India Limited	1.3 LT diesel engine Swift, Swift-Dzire, Ertiga, Breeza, Ciaz, Ritz	Valve stem seal	5.6x11.7x9.7
Car	VKS 6906	Tata Motors Ltd.	Indica V2/ Indigo eCS/Indigo XL Tdi/Indigo eCS/Indigo XL Bifuel/Zest/Bolt	Valve stem seal	7x11x14.4x9.5
Car	VKS 6916	Mahindra & Mahindra	All Jeep models with AVL engine (Except Scorpio/Tractor (Arjun)/MDI Engine (Savari/Commander/Bolero (All models Except Power Plus/Thar)	Valve stem seal (Inlet valve)	8.7x12.5x15.9x10
Car	VKS 6918	Tata Motors Ltd.	Indica CR4/Indigo eCS/Indigo XL CR4/KITES 4 (Tiago) and 5/Movus, Safari, Safari Storm, Aria, Sumo Grande	Valve stem seal	6x8.8x12.2x10
Car	VKS 6920	Tata Motors Ltd.	Indica/Indica Vista/Indigo/Marina (MPFI only)/Kites 4 (ZICA) and 5/Tiago (Kite 4) and Tigor (Kite 5), Altroz/Nexon	Valve stem seal	5.5x8.3x11.5x8
Car	VKS 6978	Tata Motors Ltd.	Safari, Sumo (4 DL engine)	Valve stem seal	8x13.3x9.4

SKF Engineering and Lubrication India Limited
Plot No. 249 & 250, Bommasandra Industrial Area,
Phase 3, Hosur Road, Bengaluru-560 099, Karnataka, India
Phone: 0821-6645100
Fax: +91-80-61301001
Email id: sealsmys@skf.com
CIN: U23200KA1993PLC044269
Contact Lincoln at +91 88841 17588 for service related queries.

® SKF and Lincoln are registered trademarks of the SKF Group.

© SKF Group 2020
The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB 80/P2 18940 EN • September 2020

Certain image(s) used under license from Shutterstock.com.